

内部酸化法（前酸化方式）材質詳細 [一般例]

種類	材質	Ag (Wt%)	その他 (Wt%)	硬度 (Hv)	導電率 (IACS%)
● Cdフリー材					
Ag-SnO ₂ -In ₂ O ₃	M2X-1	89	11	105	75
	M2X-J	86	14	110	70
	M2X-1/3	92	8	95	80
	M2X-1/4	94	6	95	85
	NEOTACT-BX	85	15	115	65
	NEOTACT-DX	85	15	115	70
Ag-SnO ₂ -In ₂ O ₃	NEOTACT-C1X	92	8	100	75
Ag-In ₂ O ₃ -SnO ₂	M1X	85	15	100	65
	NEOTACT-C2X	89	11	110	75
Ag-SnO ₂	STANOX-CX	92	8	100	85
Ag-ZnO	NEOTACT-ZX	91	9	100	85
Ag- α	HAg	99.5	0.5	110	90
● Cd材					
Ag-CdO	TOFX-2	87	13	95	75
	TOFX-3	85	15	100	70
Ag-CdO + α	TOFMX-2N	85	15	95	75
	TOFMX-6N	82	18	100	75
Ag-CdO + α	CMX	81	19	100	60